



EN 388: 2016

3443D

CUT5 LATEX COATED GLOVE



Description

Dromex® 59YSP gloves consists of a 100% Dromex® CUT5 fibre that is lint free, UV resistant and washable with textured natural rubber coated palm and fingers for superior wet and dry grip, provides protection against cut, abrasion and puncture.

An ideal glove for handling sheet metal, glass and much more.

Designed for a multiple range of industries and risks exposure. An ideal glove for automotive, assembling, packaging, warehousing both indoor and outdoor where toughness and dexterity are needed.

Special Instructions

Although the manufacturer has examined these gloves under the system for ensuring quality of production by means of monitoring and inspection, we recommend that all gloves should be thoroughly inspected before use to ensure no damage is present.

None of the materials or processes used in the manufacture of these products are known to be harmful to the wearer. The gloves and information contained herein are designed to accommodate the basic safety requirements and standards for Personal Protective Equipment. Actual conditions of use cannot be directly simulated in a test environment, therefore it is the responsibility of the user and not the manufacturer or supplier to determine the suitability for intended use.

Compliance & Conformity

Complies with the requirements of CE type examinations

EN ISO 21420:2020 for innocuousness, approved to EN 388:2003 (4,5,4,2)* previous standard and EN 388:2016 + A1:2018, (3, 4, 4, 3, D)** revised standard regulation (EU) 2016/425 for Mechanical Risks. Quality System conforms to ISO 9001:2015.

*Dromex MACH 59YSP, EN 388:2003 is rated at a cut 5 level performance **Dromex MACH 59YSP, EN 388:2016 is rated at a cut level 4, and class D performance due to the change of method in cut resistance testing methods.

Specifications

Style:	Natural rubber coated palm and fingers
Liner:	100% Dromex [®] Cut5 fibre
Palm:	2mm ± 5 %
Back:	1.5mm ± 5 %
Cuff:	Knit wrist
Mass:	±142g per pair

Packaging, Storage & Obsolescence

Packed 12 pairs per bundle and 120 pairs per carton for shipping.

Store in a cool, dry, dark place.

Stored correctly, the gloves physical properties will not change for up to three years.

59YSP

Cleaning & Maintenance

Gloves should not be left in a contaminated condition if re-use is intended especially if potential hazards exist. Before removal from the hands excess contaminant should first be removed from the glove. Should this not be possible, it is advisable to ease left and right hand gloves off using the gloved hand and remove the gloves without the contaminant contacting the bare hands.

The gloves may then be decontaminated as indicated below.

Wash up to	Do not use	Tumble dry	Do not	Do not
40C	chlorine	possible	iron	dry clean
40C	\boxtimes	•	\bigotimes	\bigotimes

In order to maximise the glove life cycle, we recommend the mildest possible cleaning conditions in terms of temperature, chemicals and cycle duration.

Due to a wide variety of possible constructions and combinations with other materials we recommend to always consult your professional cleaning service to determine the best suitable cleaning method.

Disposal

All industrial waste should be disposed of correctly according to local regulations and good disposal practice. Gloves should be disposed of considering the hazardous substance they were used for. Please consider recycling.

Sizes Available

Code	Size	Palm Length	Cuff Colour
59YSP-8	S/M	95mm (±2mm)	Yellow
59YSP-9	M/L	100mm (±2mm)	Brown
59YSP-10	L/XL	105mm (±2mm)	Black
59YSP-11	XL/XXL	110mm (±2mm)	Blue

* As per the EN420 standard, actual measurement of gloves are determined by the manufacturer, taking into account the behaviour of the glove material, its thickness (such as leather gloves, PVC gloves etc), elasticity and the intended use.

* Sizing charts only serve as a guide. Sizes and measurements are for reference only. In order to make an informed decision, always try on the gloves as each glove features a unique construction to accomodate a wearer's preferences.

Measurement Guide



1. Wing thumb 2. Rubber coated palm & fingers 3. Knit wrist

Marking

Materials



Dromex: Unit 1, 1 Blase Road, New Germany, 3620, South Africa T. +27(31) 713 1960 E. info@dromex.co.za www.dromex.co.za

Latest update: 24/03/2023 Disclaime Dromex reserves the right to make changes without further notice to any products herein to improve function, design or reliability and validity. Dromex does not assume any liability arising out of the application or use of any product described herein. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner