



RUBBER HOUSEHOLD GLOVES
DG-HS-Y and DG-HS-B



DG-HS-Y

DG-HS-B

Description

Dromex® DG-HS series of re-useable flocked lined, soft touch household gloves are designed to protect the users' hands from the hazards of water and dirt whilst keeping them dry and breathable.

Available in yellow and blue, with diamond pattern palm provides grip especially when used in wet conditions. Diamond pattern wrist cuff and flock lining assists with ease of removal on gloves. The 10cm flute cuff also allows the glove to breathe and provides a good seal over chemical protective suit or on hands.

Suitable for use when working in laboratories, cleaning, janitorial and household applications where protection of the hand is required against dust and dirt.

Special Instructions

Although the manufacturer has examined these gloves under the system for ensuring quality of production by means of monitoring and inspection, we recommend that all gloves should be thoroughly inspected before use to ensure no damage is present.

None of the materials or processes used in the manufacture of these products are known to be harmful to the wearer. The gloves and information contained herein are designed to accommodate the basic safety requirements and standards for Personal Protective Equipment. Actual conditions of use cannot be directly simulated in a test environment, therefore it is the responsibility of the user and not the manufacturer or supplier to determine the suitability for intended use.

Compliance & Conformity

Performs equivalent to the requirements of CE type examinations EN 420 for innocuousness.

Specifications

Style: Flock lined, reusable, waterproof latex gloves with wing thumb and diamond pattern palm and wrist.
 Liner: Cotton flock lined latex.
 Palm: Cotton flock lined latex 0.4mm ± 5 %
 Back: Cotton flock lined latex 0.31 mm ± 5 % impact protection.
 Cuff: 0.4mm, 10 cm Rolled cuff with diamond pattern for easier removal of glove.
 Mass: Part number DG-HS-Y ± 57 g per pair (XL); Part number DG-HS-B ± 156 g per pair (size L).

Sizes Available

Part number DG-HS-Y = sizes S – XL;
 Part number DG-HS-B = sizes S - L.

Packaging, Storage & Obsolescence


Packed in individual polybags and sold as 120 pairs per carton for shipping. Store away from humidity, in a cool, dry, dark place. Stored correctly, the gloves physical properties will not change for up to 18 months.



Cleaning & Maintenance

Gloves should not be left in a contaminated condition if re-use is intended especially if potential hazards exist. Before removal from the hands excess contaminant should first be removed from the gloves. Should this not be possible, it is advisable to ease left and right hand gloves off, using the gloved hand and remove the gloves without the contaminant contacting the bare hands.

The gloves may then be decontaminated as indicated below.



The 10142 gloves have proven that dry cleaning as well as laundering are suitable cleaning methods. We recommend that no bleaching or oxidising ingredients or any fabric softeners be used. Recommended washing temperature is between 40°C and 60°C (104 ~140°F) with mild detergents. The drying process may cause felting on the fabric surface. Drying temperature should not exceed 60°C (104 ~140°F). There is no remarkable impact on cut resistance during the normal life cycle of the glove. Depending on gloves construction, staining and cleaning method, the differences in shrinkage, yarn strength and colour may occur.

In order to maximise the gloves life cycle, we recommend the mildest possible cleaning conditions in terms of temperature, chemicals and cycle duration.

Disposal

All industrial waste should be disposed of correctly according to local regulations and good disposal practice. Gloves should be disposed of considering the hazardous substances they were used for. Please consider recycling.

Materials

